

Curtain Track Measure Sheet

Date of Order: _____	Order Reference: _____	Date Required: _____
Company Name: _____	Contact: _____	Telephone Number: _____
Delivery Address: _____		
Site Contact: _____	Telephone Number: _____	Customer Signature: _____

System Number	Colour	Qty	* Child Safety Device (Integral 10483)	Overall Width	Location	** Installation Height:	Input LH / RH or B	Input T / F or A	Bracket number if known or projection in mm	Method	****Enhanced Wave	Cord Drop	Wave Tracks please tick	
			*** Left / right or both side operation				Top or Face fixing or Adjustable brackets	LH / RH / Pair or Centre Stacking		Option 1, 2, 3, None	If face 11201 bkt = 60mm 11202 bkt = 80mm 60mm 80mm			
			Y / N										<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>
													<input type="checkbox"/>	<input type="checkbox"/>

Please Note: For multiple stack please include diagram
 When Face fixing Wave: 60mm Wave uses 11201 bracket as standard
 80mm wave uses 11202 bracket as standard
 * Child Safety Device applicable to System 3840 only complete with Silent Gliss Colorama Wave Curtains only
 ** If the Installation Height is known - cord drops will comply with EN13120
 *** If B for both, intermediate pulley will be added at extra cost
 ****Enhanced Wave
 Option 1 - 2255 Adjustable Brake
 Option 2 - 2255 Adjustable Brake & 6366 Carrier
 Option 3 - Enhanced Wave (80mm Only)

Child Safety Legislation EN 13120

Operating loop for Child Safety Device		Operating loop for chain retainer	
Installation Height	Chain Length	Installation Height	Chain Length
Known	Distance from floor to bottom of pull cords shall be at least 0.6m	Known	Distance from floor to bottom of operating chain shall be at least 1.5m
Unknown	Less than or equal to 2/3rd drop of the blind	Not Known drop ≤ 2.5m	Length of operating chain loop shall be ≤1m
		Not Known drop > 2.5m	Shall be ≤ drop of blind less 1.5m